


# P3 Comforts Furniture washbasin asymmetric # 2334100000 / 2334100030 / 2334100060

| &lt; 41 3/8" Inch &gt; |



Furniture washbasin asymmetric	Dimension	Weight	Order number
with overflow, with tap platform, overflow clip Chrome included, bowl on right side, hardware included, wall-mounted, 41 3/8" Inch			
<b>Colors</b>			
00 White			
<b>Variant</b>			
●	41 3/8" x 19 1/2" Inch	59.5 lb	2334100000
● ● ●	41 3/8" x 19 1/2" Inch	59.5 lb	2334100030
☒	41 3/8" x 19 1/2" Inch	59.5 lb	2334100060
Sanitary ceramics with the special WonderGliss surface finish will remain clean and attractive-looking for a long time to come. When ordering WonderGliss please add a "1" as eleventh digit to the model number.			
Space-saving siphon	1 1/4" Inch	0.9 lb	005076
<b>Suitable products</b>			
Vanity unit wall-mounted 1 pull-out compartment, for P3 Comforts # 233210, 233310, 233410, 40 1/8" x 19" Inch	40 1/8" x 19" Inch		LC6150
Vanity unit wall-mounted 2 drawers, upper drawer including cut-out for siphon and siphon cover, for P3 Comforts # 233410 basin right, 40 1/8" x 19" Inch	40 1/8" x 19" Inch		LC6252
Vanity unit floorstanding 2 pull-out compartments, for P3 Comforts # 233210, 233310, 233410, 40 1/8" x 19" Inch	40 1/8" x 19" Inch		LC6602

**P3 Comforts Furniture washbasin asymmetric # 2334100000 /  
2334100030 / 2334100060**

|< 41 3/8" Inch >|

Vanity unit floorstanding 2 pull-out compartments, plinth panel with integrated plinth leg (adjustable), for P3 Comforts # 233210, 233310, 233410, 40 1/8" x 19" Inch	40 1/8" x 19" Inch	LC6614
Siphon cover for # 233155, 233160, 233165, 233265, 233285, 233210, 233212, 233385, 233310, 233312, 233485, 233410, 233412, 6 3/4" x 11 3/4" Inch	6 3/4" x 11 3/4" Inch	085837
Pedestal for # 233155, 233160, 233165, 233265, 233285, 233210, 233212, 233385, 233310, 233312, 233485, 233410, 233412, 6 7/8" x 8 1/4" Inch	6 7/8" x 8 1/4" Inch	085836

*All drawings contain the necessary measurements which are subject to standard tolerances. They are stated in inch & mm and are non-binding. Exact measurements, in particular for customized installation scenarios, can only be taken from the finished ceramic piece.*