PLUG INTO POWER AND CONVENIENCE

with NuTone Inlets.

Turn to the source for power and intelligence. NuTone's line of central cleaning inlets include built-in, low-voltage terminals where direct-connect hoses plug right into the inlet – alleviating the need for a power cord. The electrified inlets make it a simple one-step operation to plug in a current-carrying hose.

The system turns on automatically when an unswitched hose is inserted or is ready for immediate activation with a switched hose.

NuTone inlets are the source of ease and convenience when working with a central vacuum system.

ELECTRIFIED INLETS

Electrified Inlets make it a simple one-step operation to plug in a current-carrying hose – no 120V extension cord to carry around. Compatible with NuTone CH615.



CI399 Series

Electra-Valve® II

The Electra-Valve® II Electrified Inlet includes a built-in, low-voltage terminal so direct-connect hoses plug right in – alleviating the need for a power cord. The molded power receptacle clips to a mounting plate and the housing wire is run to the nearest outlet box.

- UL listed Assembly
- Available in white or almond



CI358W

Supervalue

The Supervalve Electrified Inlet operates on standard house wiring. Includes wall valve, rough-in plate with junction box and strain relief.

• UL listed assembly

CI399RK

Electra-Valve® II Rough-In Kit

The Electrified Inlet Rough-In Kit includes everything you need to install the CI399. Includes mounting plate, snap-in power receptacle, plaster guard, CF382S elbow and mounting screws for plaster guard.



		INLET TYPE						
			CI399W	CI358W	360W	330W	CF372	
1035	Current Carrying	CH615	•	•			•	
		*CH515	0	0	•	•	•	
	Low Voltage	372			0	0	•	
		CH235	0	0	•	•	0	
		CH230L	0	0	•	•		

^{*} Includes 6' line cord • Full Function • Limited Function (suction only/non-powered)